

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5699-108

Township

Enjoy the simple elegance of traditional styling in this three-light wall lantern. Township's clear beveled glass and Oil Rubbed Bronze finish contains notes of New England-inspired style for this new outdoor lantern collection.

- New England-inspired style.
- Simple elegance of traditional styling.
- Clear beveled glass.

Category: Outdoor

Finish: Oil Rubbed Bronze (hand painted)

Construction: Aluminum construction

Glass/Shade: Clear Beveled glass panels



Width: 8"

Height: 22"

Depth: 10-1/2"

H/CTR: 4-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 4.5" W., 8" ht., 1" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Three 60w max. Candelabra Base E12 base phenolic sockets	cCSAus Wet location listed 1 year warranty