

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5716-108

Meadowlark

Two-light medium outdoor wall lantern with casual European style with water seeded glass panels finished in Oil Rubbed Bronze. Features unique arched roof, top ribbon scrolled loops with arching arms and shepherd's crook. Cast aluminum construction with powder coat finish.

- Two-light medium outdoor wall lantern with casual European style.
- Features unique arched roof, top ribbon scrolled loops with arching arms and shepherd's crook.
- Cast aluminum construction with powder coat finish.
- Water seeded glass panels.

Category: Outdoor

Finish: Oil Rubbed Bronze (painted)

Construction: Cast aluminum Construction

Glass/Shade: Water seeded glass panels



Width: 7-1/4"
Height: 14-1/2"
Depth: 8-1/4"
H/CTR: 7-3/4"

Glass

Width: 5-7/8"

Height: 9-1/4"

Height: 8-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate 4.625" W., 8.5" ht.	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. Candelabra Base E12 base phenolic sockets	UL-CUL Wet location listed 1 year warranty