

Brookside LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Brookside LED Collection Wall Lantern

Specifications:

- Gilded Iron, Painted White Inside Metal Shade
- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.8125 in W., 1.1875 in ht., 4.8125 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,211/71.2 (LM-82)
Lumens/LPW (Delivered)	751/43.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

P5723-7130K9



Dimensions:

Width: 12 in
 Height: 12-1/4 in
 Depth: 13-1/4 in
 H/CTR: 6-7/8 in

Gilded Iron, Painted White Inside Metal Shade
 Diameter: 12 in
 Height: 4 in

White Acrylic Diffuser
 Width: 6 in
 Height: 1 in



P5723-7130K9

Dimming Notes:

P5723-7130K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.