

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5772-09

Roman Coach CFL

Solid one-light 7" CFL wall lantern in rich finish is complemented by seeded glass panels - a great choice for low maintenance and years of enjoyment. Can be installed with or without tail. Brushed Nickel finish.

- Brushed Nickel finish.
- Etched seeded glass curved panels.
- Rich weathered style.
- Meets California Title 24.

Category: Outdoor

Finish: Brushed Nickel (plated)

Construction: Aluminum Construction

Glass/Shade: Etched Seeded glass curved panels



Width: 7"
Height: 19-5/8"
26-3/4" with tail
Depth: 6-7/8"
H/CTR: 16-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Back plate covers a standard 4" octagonal recessed outlet box</p> <p>4.75" W., 5.5" ht., 0.75" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 26w max. GU-24</p> <p>GU24 base plastic socket</p>	<p>cCSAus Wet location listed</p> <p>1 year warranty</p> <p>Meets California Title 24 high efficacy requirements for outdoor use only</p>