

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |
| Contact: | | |

Two-Light Wall Lantern

Wall vertical only mounted • Wet location listed PROGRESS LED



Description:

Clean lines are up front and center for these modern LED outdoor sconces. Valera features a die-cast aluminum frame and matte white, acrylic diffuser. Energy efficient LED source offers 3000K color temperature and 90+CRI output. Title 24 compliant. Two-light 9w LED wall lantern in a Brushed Nickel finish.

Specifications:

- Brushed Nickel (-09) (plated)
- Aluminum Construction
- Matte White acrylic diffuser
- LED Module is replaceable (part # 93054049)
- · Modern LED outdoor sconce.
- · Clean lines are central to design.
- · Features a die-cast aluminum frame and matte white, acrylic diffuser.
- 623 lumens 69.2 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Wall mount vertical only.
- Dimmable to 10% brightness (See Dimming Notes)
- Chassis covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" ADA
- · ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

| Number of Modules | 2 | |
|------------------------|--|--|
| Input Power | 9w per module | |
| Input Voltage | 120 V | |
| Input Frequency | 60 Hz | |
| Lumens/LPW (Source) | 623/69.2 (LM-82) per module | |
| Lumens/LPW (Delivered) | 640/41 (LM-79) | |
| CCT | 3000 K | |
| CRI | 90+ | |
| Life (hours) | 60,000 (L70/TM-21) | |
| FCC | Meets FCC Title 47, Part 15 Class B | |
| Min. Start Temp | -30 °C | |
| Max. Operating Temp | 30 °C | |
| Warranty | 5 year warranty | |
| Labels | cCSAus Wet location listed | |
| | ENERGY STAR® qualified | |
| | Meets California Title 24 high efficacy requirements | |
| | | |

for outdoor use only

P5806-0930K9

Images:



Dimensions:

Width: 5-5/8' Depth: 4" Height: 16" H/CTR: 8"

Glass Width: 3-3/4" Length: 5-3/8" Height: 15-15/16"



Two-Light Wall Lantern

Wall vertical only mounted • Wet location listed PROGRESS LED



P5806-0930K9

Dimming Notes:

P5806 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.