

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5806-09

Valera

Two-light outdoor, energy efficient CFL linear wall lantern finished in Brushed Nickel.

- Brushed Nickel finish.
- White acrylic diffuser.
- Energy efficient.
- Meets California Title 24.

Category: Outdoor

Finish: Brushed Nickel (Plated)

Construction: Die-cast aluminum construction, steel back plate

Glass/Shade: White polycarbonate diffuser



Width: 5-5/8"
Height: 16-1/8"
Depth: 4"
H/CTR: 8"

Glass
Width: 5-3/8"
Length: 16"
Height: 3-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall vertical mounted Mounting strap for outlet box included Backplate covers a standard 4" octagonal recessed outlet box	Pre-wired 6" of wire supplied 120 V	Quantity: Two 18w max. GU-24 GU24 base plastic sockets	cCSAus Wet location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use only