

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Compact fluorescent

# P5821-20

## Milford

One-light energy efficient CFL wall lantern with transitional styling stepped roof and white acrylic panels in an Antique Bronze finish. Cast aluminum construction.

- One-light energy efficient CFL wall lantern.
- Transitional styling stepped roof.
- White acrylic panels in an Antique Bronze finish.
- Cast aluminum construction.
- Meets California Title 24.

**Category:** Outdoor

**Finish:** Antique Bronze (painted)

**Construction:** Cast aluminum construction

**Glass/Shade:** White acrylic diffuser



**Width:** 5-3/4"  
**Height:** 8-3/4"  
**Depth:** 4-5/8"  
**H/CTR:** 5-1/8"

Glass

Width: 3"

Height: 5-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Back plate 5.375" W., 8.375" ht., 0.6875" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  One 13w max. GU-24  GU24 base socket	cCSAus Wet location listed  1 year warranty  Meets California Title 24 high efficacy requirements for outdoor use only