

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P5826-31

Cast Lantern

Make sure friends and relatives know right away where your house is when you decorate with this striking wall lantern in a black finish. With shatter-resistant acrylic panels, this outdoor lighting excels in both form and function. Cast aluminum wall lantern with beveled clear acrylic, shatter-resistant panels.

- Progress Lighting outdoor lantern constructed using cast aluminum.
- Black finish.
- Shatter resistant clear acrylic diffuser.
- Wall lantern uses one 75-watt incandescent bulb for ample illumination.
- Outdoor lighting for contemporary and modern homes.
- CSA listed.
- 1-year limited manufacturer warranty.

Category: Outdoor

Finish: Black (powder coat paint)

Construction: Cast aluminum construction

Glass/Shade: Clear Beveled acrylic shatter resistant diffuser



Width: 7" Height: 14-1/8" Depth: 10-1/4" H/CTR: 10-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate4.9375" W., 8.25" ht.	Pre-wired 6" of wire supplied 120 V	Quantity: One 75w max. Medium Base E26 base porcelain socket	UL-CUL Wet location listed 1 year warranty