

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5843-31WB

Non-Metallic

One-light polycarbonate lantern with white acrylic diffuser. CFL Bulb included.

- Black finish.
- White acrylic panels.
- Meets California Title 24.

Category: Outdoor

Finish: Black (Painted)

Construction: Polypropylene Construction

Glass/Shade: White acrylic panels



Width: 8"
Height: 17"
Depth: 8-1/4"
H/CTR: 10"

Glass
Width: 5-5/16"
Height: 5-1/2"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---|---|--|
| Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box | Pre-wired 6" of wire supplied 120 V | Quantity: One 18w max. GU-24(included) GU24 base plastic socket | UL-CUL Wet location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use only |