

## **One-Light Outdoor**

#### Project:

Fixture Type: Location:

Contact:

Wall mounted • Wet location listed PROGRESS LED



### P5862-2030K9

Images:

Westport LED offers traditional styling to complement a variety of home decor options. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. 3000K, 90+ CRI 623 lumens (source). One-light LED wall mount.

#### **Specifications:**

**Description:** 

- · Antique Bronze (-20) (powder coat paint)
- Die-cast aluminum Construction •
- Etched Seeded glass shade .
- . LED Module is replaceable (part # 93054049)
- Traditional styling.
- Softly diffused seeded glass shade. .
- . Complements many home decor styles with beaded detailing.
- · 623 lumens 69.2 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box •
- Mounting strap for outlet box included
- . 6" of wire supplied
- . ENERGY STAR<sup>®</sup> qualified
- · Meets California Title 24 high efficacy requirements for outdoor use only

#### **Performance:**

|                        |  | Dimen                                     |
|------------------------|--|---|
| Number of Modules      | 1  | Width: 6<br>Depth: 8<br>Height:<br>H/CTR: |
| Input Power            | 9w   |   |
| Input Voltage          | 120 V  |   |
| Input Frequency        | 60 Hz  |   |
| Lumens/LPW (Source)    | 623/69.2 (LM-82)                                     |   |
| Lumens/LPW (Delivered) | 322/42.3684210526316 (LM-79)                         | Glass<br>Width: 5<br>Length:<br>Height:   |
| ССТ                    | 3000 K   |   |
| CRI                    | 90 CRI   |   |
| Life (hours)           | 60,000 (L70/TM-21)                                   |   |
| FCC                    | Meets FCC Title 47, Part 15 Class B                  |   |
| Min. Start Temp        | -30 °C   |   |
| Max. Operating Temp    | 30 ℃   |   |
| Warranty               | 5 year warranty                                      |   |
| Labels                 | cCSAus Wet location listed                           |   |
|                        | ENERGY STAR <sup>®</sup> qualified                   |   |
|                        | Meets California Title 24 high efficacy requirements |   |
|                        | for outdoor use only                                 |   |
|                        |  |   |



6-7/8" 8-3/8" t: 10-1/4" R: 3-1/8"

5" n: 5" t: 4-1/4"



# One-Light Outdoor

Wall mounted • Wet location listed PROGRESS LED



## P5862-2030K9

#### **Dimming Notes:**

P5862 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls**

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.