

DATE:

NAME:

PROJECT:

Compact fluorescent

P5875-31WB Ashmore CFL

TYPE:

Ashmore collection features quill scrolled arms, decorative finials with etched water glass in a die-cast aluminum construction. One-light CFL wall lantern. Bulb included. Black finish.

- Textured Black finish.
- Etched water seeded glass curved panels.
- Quill-scrolled arms and decorative finials.
- Meets California Title 24.

Category: Outdoor

Finish: Black (powder coat paint)

Construction: Die-cast aluminum Construction, solid brass interior

components

Glass/Shade: Etched, water seeded glass curved panels



Width: 8-3/8" Height: 16-5/8" Depth: 10-1/2" H/CTR: 4-1/2"

Glass Width: 5-13/16" Height: 6.-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	cCSAus Wet location listed
Mounting strap for outlet box included	6 feet of wire supplied	One 26w max. GU-24(included)	1 year warranty
Back plate covers a standard 4" octagonal recessed outlet box	120 V	GU24 base plastic socket	Meets California Title 24 high efficacy requirements for outdoor use only
4.5" W., 9" ht.			