

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5881-30WB

Non-Metallic

One-light polycarbonate lantern with white acrylic diffuser. CFL Bulb included.

- White finish.
- White acrylic diffuser.
- Meets California Title 24.

Category: Outdoor

Finish: White (White)

Construction: Polypropylene Construction

Glass/Shade: White acrylic diffuser



Width: 6"
Height: 8-7/8"
Depth: 6-7/8"
H/CTR: 4-1/8"

Glass
Width: 5"
Height: 5-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Back plate covers a standard 4" octagonal recessed outlet box</p> <p>4.4375" W., 5.25" ht.</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 18w max. GU-24(included)</p> <p>GU24 base plastic socket</p>	<p>UL-CUL Wet location listed</p> <p>1 year warranty</p> <p>Meets California Title 24 high efficacy requirements for outdoor use only</p>