

Project:		
Fixture Type:		
Location:		
Contact:		

P5985-20MD

Roman Coach

This wall lantern offers low maintenance for years of enjoyment. The frame is coated in a handsome antique bronze finish. The lantern gently houses an etched seeded glass shade that adds extra visual texture.

- The lantern gently houses an etched seeded glass shade that adds extra visual texture.
- The frame is coated in a handsome antique bronze finish.
- $\boldsymbol{\cdot}$ This wall lantern offers low maintenance for years of enjoyment.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional settings.
- Measures 4-5/8-inch width by 10-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality.}$

Category: Outdoor

Finish: Antique Bronze (Painted)
Construction: Aluminum Construction
Glass/Shade: Etched Seeded glass Panel



Width: 4-5/8 in Height: 10 in Depth: 6-1/8 in H/CTR: 2-3/4 in

Etched Seeded glass Panel

Width: 3-3/8 in Height: 6-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Manualla and an a famous Hall have	Cinalan aforina accaminal		1
Mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.562" W., 4.562" ht., 2.375" depth			