

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P5986-20MD

Roman Coach

This wall lantern offers low maintenance for years of enjoyment. The frame is coated in a handsome antique bronze finish. The lantern gently houses an etched seeded glass shade that adds extra visual texture.

- The lantern gently houses an etched seeded glass shade that adds extra visual texture.
- The frame is coated in a handsome antique bronze finish.
- This wall lantern offers low maintenance for years of enjoyment.
- Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for transitional settings.
- Measures 4-5/8-inch width by 6-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Aluminum Construction

Glass/Shade: Etched Seeded glass Panel



Width: 4-5/8 in
Height: 6-1/2 in
Depth: 6-1/8 in
H/CTR: 2-3/4 in

Etched Seeded glass Panel
Width: 3-3/8 in
Height: 4-7/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---------------------------|--|----------------------------|
| Wall mounted | Prewired | Quantity: | CCSAus Wet Location Listed |
| Mounting strap for outlet box included | 6 inches of wire supplied | One 100 W max. Medium Base or LED equivalent | 1-year Limited Warranty |
| Canopy covers a standard 4" recessed outlet box: 4.562" W., 4.562" ht., 2.375" depth | 120 V | E26 base Porcelain socket | |