

Project:			
Fixture Type:			
Location:			
Contact			

P5986-31MD

Roman Coach

This wall lantern offers low maintenance for years of enjoyment. The frame is coated in a handsome black finish. The lantern gently houses an etched seeded glass shade that adds extra visual texture.

- This wall lantern offers low maintenance for years of enjoyment.
- · The frame is coated in a handsome black finish.
- The lantern gently houses an etched seeded glass shade that adds extra visual texture.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional settings.
- Measures 4-5/8-inch width by 6-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Aluminum Construction **Glass/Shade:** Etched Seeded glass Panel



Width: 4-5/8 in Height: 6-1/2 in Depth: 6-1/8 in H/CTR: 2-3/4 in

Etched Seeded glass Panel

Width: 3-3/8 in Height: 4-7/8 in

	MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
	Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Mounting strap for outlet box included		6 inches of wire supplied	LED equivalent	1-year Limited Warranty
		120 V	E26 base Porcelain socket	
	Canopy covers a standard 4" recessed outlet box: 4.562" W., 4.562" ht., 2.375" depth			