

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Halogen

P6161-09WB

Directional

Four-light round back wall or ceiling mount directional. Transitional design in a Brushed Nickel finish will be a stylish complement to your decor. Four independently adjustable track heads to direct and focus light where needed - track heads rotate 350-degrees and has a 60-degree tilt. MR16 bulbs included.

Width: 36-3/16"

Height: 5"

Depth: 4-3/4"

- Brushed Nickel finish.
- Multi Directional Light
- Wall or ceiling mount.
- Round Back.
- This product is not available for sale into the State of California.

Category: Directionals

Finish: Brushed Nickel (plated)

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or ceiling mounted Mounting strap for outlet box included Back plate 5.125" W., 5.125" ht.	Pre-wired 6" of wire supplied 120 V	Quantity: Four 50w max. MR-16(included) GU10 base ceramic sockets	cCSAus Damp location listed 1 year warranty