

P6342 SERIES FLOOD

Fixture mounted • Wet location listed



Description:

The LED swivel flood light has tempered glass and rugged die-cast construction. For complete fixture order with P6343 backplate. 1,115 lumens 3000K color temperature, 83 CRI. 1/2" NPS treaded mounting. Adjustable swivel for easy adjustment. IP65 rated.

Specifications:

- Antique Bronze (-20), Bright White (-28), Metallic Gray (-82) (powder coat paint)
- Die-cast aluminum construction
- Tempered glass lens
- Dimmable to 10% brightness (See Dimming Notes)
- 6" of wire supplied

Performance:

Number of Modules	1
Input Power	13w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1115/84.5 (LM-79)
CCT	3000 K
CRI	83
Life (hours)	60,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Wet location listed

P6342 SERIES

Images:



Dimensions:

Diameter: 3-3/4"
Length: 3-3/4"
Height: 5"
Depth: 3-1/4"