

## One-Light Outdoor

Post top - fitter for 3" post or pedestal mounted • Wet location listed



### Description:

Arrive LED lanterns feature a die-cast aluminum, powder coated frame and heavily textured glass. One-light post wall lantern. 90+ CRI, 3000K, 1,211 lumens 71.2 lumens/watt per module (source).

### Specifications:

- Black (-31) (painted)
- Die-cast aluminum Construction
- Clear Seeded glass panels
- LED Module is replaceable (part # 93053641)
- Die-cast aluminum, powder coated frame.
- Heavily textured glass.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Mounting No for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only
- Dark Sky friendly

### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	689/41.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Wet location listed ENERGY STAR® qualified Meets California Title 24 high efficacy requirements for outdoor use only

## P6427-3130K9

### Images:



### Dimensions:

Square: 9"  
Height: 15-7/8"

Glass  
Width: 0-1/8"  
Length: 6"  
Height: 9-1/8"

## P6427-3130K9

### Dimming Notes:

---

P6427 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Nova T NTELV-300

Lutron Vieri VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.