

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P6433-09

## New Haven

A Brushed Nickel finish complements clear beveled glass in the New Haven outdoor post lantern. Durable aluminum construction. Fits 3" post (order separately). Post, hanging and wall options are available.

- Brushed Nickel finish.
- Clear beveled glass.
- Fits 3" post (order separately).

**Category:** Outdoor

**Finish:** Brushed Nickel (plated)

**Construction:** Aluminum Construction

**Glass/Shade:** Clear Beveled glass panels



**Diameter: 11"**  
**Height: 23"**

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post top - fitter for 3" post or pedestal mounted  Mounting No for outlet box included  3.1875" W., 3" ht., 3.1875" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  Three 60w max. Candelabra Base  E12 base phenolic socket	cCSAus Wet location listed  1 year warranty