

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P6438-31

Andover CFL

The Andover collection one-light post lantern with cast aluminum construction, offers a mixture of traditional and country style for a variety of applications. The etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light. Uses GU24 base compact fluorescent lamps for energy efficiency.

- Clear seeded water glass panels
- Etched pillar diffuser.
- GU24 sockets for use with energy efficient bulbs.
- Meets California Title 24.

Category: Outdoor

Finish: Black (powder coat paint)

Construction: Aluminum Construction

Glass/Shade: Water Seeded glass



Diameter: 9-1/2"

Height: 22-3/8"

Glass

Width: 7-3/8"

Height: 7-11/16"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|---|--|
| Post top - fitter for 3" post or pedestal mounted Mounting No for outlet box included 3.25" W., 2.8125" ht., 3.25" depth | Pre-wired 6" of wire supplied 120 V | Quantity: One 26w max. GU-24 GU24 base socket | cCSAus Wet location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use only |