

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P6440-31MD Crawford

Crawford Collection One-Light Traditional Textured Black Etched Glass Outdoor Post Light

**Category:** Outdoor

**Finish:** Textured Black (Painted)

**Construction:** Cast Aluminum Construction

**Glass/Shade:** Etched Glass Panel



Diameter: 9-7/8 in  
Height: 24-5/8 in

Etched Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Post Mount	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per socket	
		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	