

### Incandescent

# 6" 45 Degree Slope


Recessed

Ceiling Housing
IC & Air Tight

Type		

P645-AT □

		Dimensions (Inches)			
Catalog No.	Lamping	Α	В	C	
P645-AT	75BR30/PAR30	13	8-3/8	7-5/8	
		6-7/8	eilina op	enina	



### **Specifications:**

### Wiring

- Universal heavy gauge junction box
- Knock out free universal Romex clamps
- Access door in housing for field inspection of wiring
- Universal J-box with snap-out sides
- Grounding pigtail
- 1/2" & 3/4" pryouts for grid conduit or BX fittings

### Construction

- All aluminum outer housing
- Fits into 2x8 construction
- Notched housing for chalking alignment
- Ceramic socket
- Housing adjusts from 1/2" to 1-1/2" thick ceilings

### Bar Hangers

- Nail grip hanger bars
- Integral T-bar ceiling clamps on hanger hars
- Hanger bars will span 24" t-bar spacing
- Bar hanger lock to secure housing in position

#### **Labeling**

- UL-CUL Damp location listed and feed through branch wiring
- IC rated
- Complies with Washington State Energy Code ((WSEC) requirement for air tight

### Lamp/Trim

- Trim-Lok action forces trim to fit snugly against the ceiling
- Trim mounted socket for optimum performance

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607




# Incandescent


# 6" 45 Degree Slope Ceiling Housing IC

Recessed

Type \_\_\_\_\_\_ P645-TG □

Catalog No.	Lamping	Dimensions (Inches)		
		A B C		
P645-TG	75w Par30/65w BR30	13 8-3/8 7-5/8		
		6-7/8 ceiling opening		





• Trim must be ordered separately.

### **Specifications:**

### Wiring

- Universal heavy gauge junction box screw-lock door
- Knock out free integral Romex clamps
- Access door in housing for field inspection of wiring
- Universal J-box with snap-out sides
- Grounding pigtail
- 1/2" & 3/4" pryouts for grid conduit or BX fittings

### Construction

- All aluminum outer housing
- Fits into 2x8 construction
- Notched housing for chalking alignment
- Porcelain socket with nickel-plated brass screw shell

### **Bar Hangers**

- Nail grip hanger bars
- Integral T-bar ceiling clamps on hanger bars
- Hanger bars will span 24" T-bar spacing
- Bar hanger locks to secure housing in position

## **Labeling**

- UL-CUL Damp location listed and feed through branch wiring
- IC rated

### Lamp/Trim

- Lamp in vertical position from 9-45 degree sloped ceiling (2/12 to 12/12)
- Lamp is adjustable from below ceiling
- Single spring attachment of trim

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607