

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P6532-108

## Maison

Two-light hanging lantern in the Maison Collection offers traditional French country styling for a variety of home settings. Classic and formal clear water seeded glass complements the powder coat finish. Oil Rubbed Bronze finish.

- Traditional French country styling.
- Classic and formal clear water seeded glass.
- Powder coat finish.

**Category:** Outdoor

**Finish:** Oil Rubbed Bronze (hand painted)

**Construction:** Aluminum Construction

**Glass/Shade:** Water Seeded glass panels



**Diameter:** 7-1/4"

**Height:** 17-7/8"

**Overall Ht. W/Chain:** 93"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.875" ht., 5" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Two 60w max. Candelabra Base E12 base phenolic sockets	UL-CUL Wet location listed 1 year warranty