

## Ceiling/Pendant

Ceiling stem hung with 6 links of chain/semi-flush mounted • Damp location listed



### Description:

The one-light hanging lantern from the Belle LED Collection features nautical undertones and a cage reminiscent of industrial spaces that is ideal for both interior and exterior settings. This fixture is available in convertible ceiling/pendant and wall mount options. LED hanging lantern. Antique Bronze finish.

### Specifications:

- Antique Bronze (-20) (painted)
- Aluminum Construction
- Etched glass diffuser
- LED Module is replaceable (part # 93054049)
- Nautical undertones.
- Cage reminiscent of industrial spaces.
- Ideal for both interior and exterior spaces.
- Includes one 6", four 12" stems and 6 Links of chain.
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 10 feet of wire supplied
- One 6", four 12" lengths of stem included
- Six links of 9 gauge chain supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

### Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	445.1/55 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 high efficacy requirements
	for outdoor use only

## P6536-2030K9

### Images:



### Dimensions:

Diameter: 6-5/8"  
 Height: 11-3/8"  
 Overall Ht. W/Stem: 77"

Glass  
 Width: 4-3/8"  
 Length: 4-3/8"  
 Height: 8-3/4"

**P6536-2030K9****Dimming Notes:**

---

P6536 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.  
Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.