

Project:

Fixture Type:

Location:

Contact:

LED Step Lights

Wall Mounted • Wet Location Listed PROGRESS LED

Description:

Led Step Light

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

| Input Power | 4.5 W |
|------------------------|------------------------------------|
| Input Voltage | 120 VAC |
| Input Frequency | 60 Hz |
| Lumens/LPW (Delivered) | 90/20 (LM-79) |
| ССТ | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 50000 (L70/TM-21) |
| EMI/RFI | FCC Title 47, Part 15, Class B |
| Warranty | 5-year Limited Warranty |
| Labels | cCSAus Wet Location Listed |
| | Meets California Title 24 JA8-2016 |

P660005-009-30



Shown in vertical installation

Shown in horizontal installation



Dimensions:

Length: 4-7/8 in (Mounted Horizontal)

Height: 3-1/32 in Depth: 1-7/8 in

Mounted inside wall/J-box

Width: 2-5/8 in Height: 1-5/8 in Depth: 1-1/8 in



LED Step Lights

Wall Mounted • Wet Location Listed PROGRESS LED

Dimming Notes:

P660005-009-30

P660005-009-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.