

Project:
Fixture Type:

Location:
Contact:

## **LED Step Lights**

Wall Mounted • Wet Location Listed PROGRESS LED

### **Description:**

Led Step Light

### **Specifications:**

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

### **Performance:**

Input Power	4.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	100/22.22 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	Meets California Title 24 JA8-2016

# P660005-028-30



Shown in vertical installation

Shown in horizontal installation



### **Dimensions:**

Length: 4-7/8 in (Mounted Horizontal)

Height: 3-1/32 in Depth: 1-7/8 in

Mounted inside wall/J-box

Width: 2-5/8 in Height: 1-5/8 in Depth: 1-1/8 in



## **LED Step Lights**

Wall Mounted • Wet Location Listed PROGRESS LED

### **Dimming Notes:**

P660005-028-30

P660005-028-30 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.