

Project: Fixture Type:

Location:
Contact:

LED Step Lights

Wall Mounted • Wet Location Listed PROGRESS LED

Description:

LED Indoor/Outdoor Black Integrated LED Wall or Step Light with Photocell

Specifications:

- Faceplate covers a standard 4" recessed outlet box
- · Includes both horizontal and vertical faceplates
- · Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:

Input Power	4.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	120/27 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	Meets California Title 24 JA8-2016





Dimensions:

Width: 4-13/16 in Depth: 1-1/2 in Height: 3 in