

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



Incandescent

# P6616-09

## Burlington

The two-light wall lantern from the Burlington outdoor collection is constructed from aluminum for durable, weather-resistant performance. A Brushed Nickel finish complements the clear beveled glass. Open bottom design allows individuals to replace lamps without removing any glass shade.

Width: 9"  
Height: 18-3/4"  
Depth: 9-3/4"  
H/CTR: 7-5/8"

- Brushed Nickel finish
- Durable aluminum construction
- Complemented by clear beveled glass
- Open bottom design allows individuals to easily replace lamps

**Category:** Outdoor

**Finish:** Brushed Nickel (plated)

**Construction:** Aluminum construction

**Glass/Shade:** Clear beveled glass panels

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Backplate covers a standard 4" hexagonal recessed outlet box	Pre-wired  6" of wire supplied  120 V	Quantity:  Two 60w max. Candelabra Base  E12 base phenolic socket	cCSAus Wet location listed  1 year warranty