PROGRESS LIGHTING[™]

Project: Fixture Type:

Location:

Contact:

P6620-31MD Andover

This wall lantern offers a mix of traditional and country styles that will complement a variety of settings. The etched pillar of glass diffuser inside the clear water seeded glass shade gives off a soft glow of light. The lantern's frame is coated in a classic black finish.

- This wall lantern offers a mix of traditional and country styles that will complement a variety of settings.
- The etched pillar of glass diffuser inside the clear water seeded glass shade gives off a soft glow of light.
- The lantern's frame is coated in a classic black finish.
- Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for transitional, new traditional, or farmhouse settings.
- Measures 7-1/2-inch width by 18-3/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- $\cdot\,$ Able to be fully dimmable with dimmable bulbs.

recessed outlet box: 4.5" W., 9.25" ht., 0.75" depth

- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Black (Painted) Construction: Cast Aluminum Construction Glass/Shade: Clear Water Seeded glass Panel, Etched Glass diffuser



Width: 7-1/2 in Height: 18-3/8 in Depth: 8-3/8 in H/CTR: 10-1/2 in

Clear Water Seeded glass Panel Width: 5-11/16 in Height: 6-1/4 in

Etched Glass diffuser Width: 3 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Canopy covers a standard 4"	120 V	E26 base Porcelain socket	