

Project:			
Fixture Type:			
Location:			
Contact:			

P6621-31MD

Andover

This wall lantern offers a mix of traditional and country styles that will complement a variety of settings. The etched pillar of glass diffuser inside the clear water seeded glass shade gives off a soft glow of light. The lantern's frame is coated in a classic black finish.

- This wall lantern offers a mix of traditional and country styles that will complement a variety
 of settings.
- The etched pillar of glass diffuser inside the clear water seeded glass shade gives off a soft glow of light.
- The lantern's frame is coated in a classic black finish.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional, new traditional, or farmhouse settings.
- Measures 9-1/2-inch width by 26-1/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Water Seeded glass Panel, Etched Glass diffuser



Width: 9-1/2 in Height: 26-1/8 in Depth: 10-1/4 in H/CTR: 12-3/4 in

Clear Water Seeded glass Panel

Width: 7-3/8 in Height: 7-11/16 in

Etched Glass diffuser Width: 3-1/2 in Height: 6-5/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 12" ht., 0.75" depth			