

Project:			
Fixture Type:			
Location:			
Contact:			

## P6626-31CD

This wall lantern has a decorative and fashion-orientated design with modern classic styling. The clear water seeded glass shade gives off a soft glow of light. The beautiful black-finished lantern frame gently holds the shade in place.

- The clear water seeded glass shade gives off a soft glow of light.
- The beautiful black-finished lantern frame gently holds the shade in place.
- This wall lantern has a decorative and fashion-orientated design with modern classic styling.
- Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional or new traditional settings.
- Measures 6-1/8-inch width by 18-7/8-inch height.
- Uses one candelabra base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Outdoor **Finish:** Black (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Water Seeded glass Panel, Etched Glass diffuser



Width: 6-1/8 in Height: 18-7/8 in Depth: 7-1/2 in H/CTR: 9-1/4 in

Clear Water Seeded glass Panel

Width: 4-7/8 in Height: 7-3/8 in

Etched Glass diffuser Width: 2-3/4 in Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Candelabra Base	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6" of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 9" ht., 0.812" depth			