

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P6628-31MD Cadence

This wall lantern has a decorative and fashion-orientated design with modern classic styling. The clear water seeded glass shade gives off a soft glow of light. The beautiful black-finished lantern frame gently holds the shade in place.

- The clear water seeded glass shade gives off a soft glow of light.
- The beautiful black-finished lantern frame gently holds the shade in place.
- This wall lantern has a decorative and fashion-orientated design with modern classic styling.
- Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for transitional or new traditional settings.
- Measures 10-inch width by 31-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Outdoor

**Finish:** Black (Painted)

**Construction:** Cast Aluminum Construction

**Glass/Shade:** Clear Water Seeded glass Panel, Etched Glass diffuser



Width: 10 in  
Height: 31 in  
Depth: 11.385 in  
H/CTR: 14-1/83 in

Clear Water Seeded glass Panel  
Width: 7-15/16 in  
Height: 11-15/16 in

Etched Glass diffuser  
Width: 3-13/16 in  
Height: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6" of wire supplied	One 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 18" ht., 1" depth	120 V	E26 base Porcelain socket	