

Project:			
Fixture Type:			
Location:			
Contact:			

P6630-31MD Crawford

This wall lantern offers updated traditional styling with scroll arm. Etched white glass panes give off a soft glow of light. The panes are housed in a beautiful black frame.

- Etched white glass panes give off a soft glow of light.
- The panes are housed in a beautiful black frame.
- This wall lantern offers updated traditional styling with scroll arm.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for transitional or new traditional settings.
- Measures 6-1/2-inch width by 12-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Etched glass Panel, Etched Glass Panel



Width: 6-1/2 in Height: 12-1/2 in Depth: 8-3/4 in H/CTR: 8 in

Etched glass Panel Width: 2-3/4 in Height: 4-7/16 in

Etched Glass Panel Width: 1-7/16 in Height: 4-7/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CCSAus Wet Location Listed
		One 100 W max. Medium Base or	
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.812" depth			