

Project:			
Fixture Type:			
Location:			
Contact:			

P6637-31MD Maison

This wall lantern offers traditional French country styling for a variety of home settings. The etched pillar of glass diffuser inside the clear water seeded glass gives off a soft glow of light. The gorgeous shade is housed in the lantern's beautiful black frame.

- The etched pillar of glass diffuser inside the clear water seeded glass gives off a soft glow of light.
- The gorgeous shade is housed in the lantern's beautiful black frame.
- This wall lantern offers traditional French country styling for a variety of home settings.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional or farmhouse settings.
- Measures 10-1/2-inch width by 23-3/4-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Water Seeded glass Panel, Etched Glass diffuser



Width: 10-1/2 in Height: 23-3/4 in Depth: 11-1/4 in H/CTR: 16-3/8 in

Clear Water Seeded glass Panel

Width: 8-1/2 in Height: 14-3/4 in

Etched Glass diffuser

Width: 4 in Height: 7-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 12.125" ht., 1.5" depth			