

Project:

Fixture Type:

Location:

Contact:

# Hide-a-lite

Undercabinet Mounted • Damp Location Listed PROGRESS LED



## **Description:**

Hide-A-Lite Collection 18" LED 5-CCT Linear Undercabinet Light

### **Specifications:**

- · Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

### **Performance:**

Number of Modules	1
Input Power	6.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	457/70 (LM-79)
ССТ	2700 K
	3000 K
	3500 K
	4000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2019





# **Dimensions:**

Length: 17-1/2 in Depth: 3-1/4 in Height: 1.05 in



# Hide-a-lite



### **Dimming Notes:**

P700026-028-CS is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

# P700026-028-CS

### **Dimming Controls:**

Eaton AAL06

IDevices IDEV009

Leviton\_Trimatron 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.