

## Hide-a-lite

Undercabinet Mounted • Damp Location Listed PROGRESS LED



# P700027-028-CS

### Description:

Hide-A-Lite Collection 24" LED 5-CCT Linear Undercabinet Light

### Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	1
Input Power	8.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	608/71 (LM-79)
CCT	2700 K 3000 K 3500 K 4000 K 5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed ENERGY STAR® qualified Meets California Title 24 JA8-2019



### Dimensions:

Length: 23-1/2 in  
Depth: 3-1/4 in  
Height: 1.05 in

# P700027-028-CS

## Dimming Notes:

---

P700027-028-CS is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Eaton AAL06

IDevices IDEV009

Leviton\_Trimatron 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.