

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Linear fluorescent

P7019-30WB

Undercabinet

Mount easily under cabinets and shelves, over a desk, in kitchens or any work area. All have a white acrylic diffuser and white baked enamel housing. Standard 120V NPF ballast and starter switch.

- White baked enamel housing.
- Mount easily under cabinets and shelves, or over a desk.
- Ideal for kitchens or any work area.
- Six feet cord and plug.
- Rocker switch

Category: Undercabinet

Finish: White (Baked Enamel)

Construction: Steel construction

Glass/Shade: White acrylic diffuser

Width: 4"
Length: 18-3/8"
Height: 1-5/8"

Glass
Width: 18.313"
Height: 2.362"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Undercabinet mounted	Pre-wired 120 V	Quantity: One 15w max. F15T8(included) Bi-pin twist-in base ceramic lamp holders	UL-CUL Damp location listed 1 year warranty