

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710016-31M Metro

Metro Collection One-Light New Traditional Matte Black Summer Linen Wall Light

**Category:** Wall Sconces

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Summer Linen Fabric Square



Width: 5-1/2 in  
Extends: 7-1/4 in  
Height: 15-1/8 in  
H/CTR: 10-1/2 in

Summer Linen Fabric Square  
Width: 5-1/2 in  
Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5" ht., 0.68" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	