

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710018-031 Bonita

Inspired at its roots by an understated beauty and a breathtaking formal elegance, this wall sconce will make a stunning addition to any luxurious living space. A black arm flows down from an ornamental light base to a rectangular backplate. On top of the light base sits a summer linen shade.

- Inspired at its roots by an understated beauty and a breathtaking formal elegance, this wall sconce will make a stunning addition to any luxurious living space.
- A black arm flows down from an ornamental light base to a rectangular backplate.
- On top of the light base sits a summer linen shade.
- Ideal for any bedroom, living room, sitting room, hallway, or foyer.
- Perfect for transitional, modern, farmhouse, contemporary, or luxury settings.
- Measures 4-1/2-inch width by 17.13-inch height.
- Uses one candelabra base bulb that is sold separately (40w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Wall Brackets

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Summer Linen fabric Shade



Width: 4-1/2 in  
Height: 17-1/8 in  
Depth: 6-7/8 in  
H/CTR: 13-5/8 in

Summer Linen fabric Shade  
Width: 4-1/4 in  
Height: 5-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CULus Damp Location Listed
Mounting backplate for outlet box included	6 inches of wire supplied	One 40 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.75" depth	120 V	E12 base Phenolic socket	