

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P710025-104

Avana

Avana features a graceful arching tapered candle-arm with a crisp geometric linen shade. The faceted backplate provides a rich architectural detail that complements many fashionable vanity styles.

- Features a graceful arching tapered candle-arm.
- The faceted backplate provides rich architectural detail.
- Arm supports a crisp, square white linen shade.
- Complements many styles of fashionable vanity pieces
- Polished Nickel finish.
- Part of the Design Series Collections offering high style and design.

Category: Sconces

Finish: Polished Nickel (plated)

Construction: Steel construction

Glass/Shade: White Linen fabric shade



Width: 5-5/8"
Height: 16"
Depth: 7-1/2"
H/CTR: 12-1/2"

Glass
Width: 5-7/16"
Height: 6-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included covers a standard 4" octagonal recessed outlet box	Pre-wired 6" of wire supplied 120 V	Quantity: One 60w max. Candelabra Base E12 base socket	cULus Dry location listed