

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

## P710031-143

## Gulliver

Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations of Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.

- Design complements Rustic and Modern Farmhouse home décor accents, as well as Urban Industrial and Coastal interior settings
- Metal banding features embossed wood grain pattern for rich visual texture
- Hand painted Graphite finish with weathered gray accents
- Dual-toned frame emulates popular design style that contains mixed metal accents
- Uses one 75 watt max, medium base lamps bulbs (sold separately)
- Shop the complete Gulliver collection for a coordinated look throughout your entire home or mix and match with other complementary styles for a more curated decor
- Can be used in hallways, entryways and foyer settings

Category: Bath & Vanity Finish: Graphite (painted)

Construction: Steel construction



Width: 6" Height: 12" Depth: 7"

H/CTR: 9-3/8" (glass facing up)

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6" of wire supplied	Quantity:	cETLus Damp location listed
Mounting strap for outlet box included	120 V	One 75w max. medium E26 base	1 year limited warranty
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" octagonal recessed outlet box			
5.125" W., 0.75" ht., 5.125" depth			