

**Description:**

Apogee Collection Wall Sconce

**Specifications:**

- Etched Glass Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" recessed outlet box: 14.875 in W., 7.5 in ht., 0.875 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

**Performance:**

Number of Modules	1
Input Power	20.8 W
Input Voltage	120-277 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	940/45.2 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class A
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016

**P710036-009-30**



**Dimensions:**

Width: 15 in  
Depth: 3-11/16 in  
Height: 7.5 in

Etched Glass Shade  
Width: 12-3/4 in  
Height: 6-3/8 in

# P710036-009-30

## Dimming Notes:

---

P710036-009-30 is designed to be compatible with many 0-10V controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_NFTV

Lutron\_NTFTV

Lutron\_DVTV

Leviton\_AWSMT-7DW

Leviton\_IP710

Lithonia\_ISD BC

Pass & Seymour\_CD4FB

Wattstopper\_ADF-120277

Hunt Dimming\_PS-010-120V

Hunt Dimming\_PS010 277V

Lightolier Controls\_MP1500FAM120

Lightolier Controls\_ZP600FAM120

Synergy Lighting Controls\_V2000FAMU

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.