

DATE:	TYPE:	
NAME:		
PROJECT:		



P710045-009

Kempsey

Kick back and relax within the pages of your favorite novel under the glow of the Kempsey one-light wall bracket. A smooth, arced arm extends from a rectangular backplate to hold the small, curved bar that supports a clean, Summer Linen shade. With an alluring Brushed Nickel finish, the fixture blends well with transitional and farmhouse interiors where it can provide focused task light while mounted to a wall in a bedroom, office, den, or living room.

- Excellent for mounting on walls in a bedroom, office, den, living room, or wherever focused light is desired for tasks or reading
- Updated, classic styling is ideal for transitional and farmhouse interiors
- A modern, wall bracket featuring a sleek, curved arm holding the textured shade
- Multi-directional arm allows the entire fixture to rotate from side to side
- On/off rotary switch on backplate
- Finished in quietly reflective Brushed Nickel with a crisp, Summer Linen shade
- Textured linen shade glows from the inside out
- Uses one 75-watt max medium base bulb, or the LED equivalent, that is sold separately
- Measures 12 in diameter X 19-3/4 in height, Extends from the wall 23-5/8 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Wall Brackets
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Summer Linen shade fabric cylindrical

Height: 19-3/4"
Depth: 23-5/8"
H/CTR: 7-1/2"
Glass

Diameter: 12"

11-1-1-1-10 2/4//

Width: 12" Length: 12" Height: 6"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	cULus Damp location listed
Mounting plate for outlet box included Fixture can be installed with glass facing up or down	6" of wire supplied 120 V	One 75w max. Medium Base E26 base Porcelain socket	
Back Plate covers a standard 4" octagonal recessed outlet box 5" W., 11.875" ht., 0.875" depth			