

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P710045-020

Kempsey

The contrast of a textured Harvest Linen shade supported by a refined, Antique Bronze wall mount makes the Kempsey one-light wall bracket ideal for providing focused task light in a bedroom, office, den, or living room. The union of the rectangular backplate and smoothed, curved arms will make an eye-pleasing piece in any transitional or farmhouse setting.

- Ideal for mounting on a wall in a bedroom, office, den, living room, or wherever focused light is desired for tasks or reading
- Updated classic styling is ideal for Transitional and Farmhouse interiors
- A modern, one-light wall bracket featuring a sleek, curved arm holding the textured shade
- Multi-directional arm allows the entire fixture to rotate from side to side
- On/off rotary switch on backplate
- Uses one 75-watt max medium base bulb, including the LED equivalent, that is sold separately
- Textured linen shade glows from the inside out
- Finished in Antique Bronze with a warm, Harvest Linen shade
- Measures 12 in diameter X 19-3/4 in height, Extends from the wall 23-5/8 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Wall Brackets

Finish: Antique Bronze (Painted)

Construction: Steel Construction

Glass/Shade: Harvest Linen shade fabric cylindrical



Diameter: 12"
Height: 19-3/4"
Depth: 23-5/8"
H/CTR: 7-1/2"

Glass

Width: 12"

Length: 12"

Height: 6"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting plate for outlet box included Fixture can be installed with glass facing up or down Back Plate covers a standard 4" octagonal recessed outlet box 5" W., 11.875" ht., 0.875" depth	Pre-wired 6" of wire supplied 120 V	Quantity: One 75w max. Medium Base E26 base Porcelain socket	cULus Damp location listed