

LED Wall Sconce

 Wall mounted • Damp location listed **PROGRESS LED**


Description:

A fresh, minimalist design with the LED Wall Sconce presents a textured Summer Linen shade that artistically disguises the cutting-edge LED light source. The elegant, simple design is perfect for brightening any wall space where soft light is desired in transitional interiors.

Specifications:

- White (-030) (Painted)
- Steel Construction
- Summer Linen fabric half cylinder shade
- Perfect for illuminating any wall space where soft light is desired
- Textured shade is ideal for transitional interiors
- One-light wall sconce with a crisp, Summer Linen half shade
- Curved form gives a sleek and minimalist silhouette
- Measures 6-1/4 in wide X 9 in height, Extends 3-1/8 in
- Uses one 9-watt LED module, 3000K, 90CRI, 624 source lumens (source)
- ADA compliant and includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Dimmable to 10% brightness (See Dimming Notes)
- Back Plate covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	30 °C
Max. Operating Temp	-30°C
Warranty	5-year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P710071-030-30

Images:



Dimensions:

Width: 6-1/4"
Depth: 3-7/8"
Height: 9"
H/CTR: 4-1/2"

Glass
Width: 6-3/16"
Length: 3-7/8"
Height: 9"

P710071-030-30

Dimming Notes:

P710071 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron	Diva	DVELV-300P
Lutron	Nova T	NTELV-300
Lutron	Caseta	
Lutron	Ariadni	AY-600P
Leviton	Illumatech	IPI06-1LZ
Leviton	SureSlide	6672
Lutron	Ariadni	AYCL-153P
Lutron	Skylark Contour	CTCL-153P
Lutron	Diva	DVCL-153P
Lutron	Toggler	TGCL-153P
Lutron	Maestro	MACL-153M
Lutron	Ariadni	AYLV-600P
Lutron	NOVA T	NTLV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Lutron	Renoir II	AWRMG-EAW
Lutron	Nova	N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.