## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P710074-031 Durrell

This versatile wall bracket from the Durrell Collection will easily find a home in a variety of settings in need of generous illumination. A light base reminiscent of a vintage candlestick is coated in a beautiful black finish. Beneath the light base, a decorative wooden piece coated in a ceruse black finish tops a long, curving metal arm. The arm attaches to a round black backplate with a faux-painted wooden center for a mixed-elements aesthetic.

- A light base reminiscent of a vintage candlestick is coated in a beautiful black finish.
- Beneath the light base, a decorative wooden piece tops a long, curving metal arm.
- A round black backplate with a faux-painted wooden center creates a mixed-elements aesthetic.
- Ideal for any foyer, hallway, dining room, or kitchen.
- Perfect for rustic, farmhouse, and coastal settings.
- Measures 4-1/2-inch width by 12-inch height.
- Uses one candelabra base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Wall Brackets Finish: Matte Black (Painted) Construction: Steel Construction

ht., 0.8125" depth

Width: 4-1/2 in Height: 12 in Depth: 5 in H/CTR: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 60 W max. Candelabra Base	CULus Dry Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E12 base Phenolic socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7"			