

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P710076-196 Cumberland

Cumberland Collection One-Light Aged Bronze Modern Farmhouse Wall Sconce

Category: Wall Sconces
Finish: Aged Bronze (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Seeded Glass



Width: 5-1/8 in
 Extends: 4 in
 Height: 14-5/8 in
 H/CTR: 7-1/4 in

Clear Seeded Glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty Americans With Disabilities Act (ADA) compliant
Back Plate covers a standard 4" recessed outlet box: 5.12" W, 14.56" ht., 0.812" depth		Dimmable to 10% brightness (See Dimming Notes)	