

Project:			
Fixture Type:			
Location:			
Contact:			

## P710082-009 Riley

Incorporate a sleek simplicity and natural beauty with the Riley Collection's One-Light Brushed Nickel Wall Bracket. A clear glass shade offers stunning illumination. The shade rests on a gorgeous dual-toned frame with a brushed nickel finish and touches of polished chrome accents. Ideal for new traditional or contemporary settings.

- The shade rests on a gorgeous dual-toned frame with a brushed nickel finish and touches of polished chrome accents.
- A clear glass shade is ready to offer stunning, rejuvenating illumination.
- Incorporate a sleek simplicity and natural beauty with this wall bracket.
- · Ideal for any bathroom.
- · Perfect for new traditional or contemporary settings.
- · Measures 5-inch width by 14-1/2-inch height.
- Uses one candelabra base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Wall Brackets
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade



Width: 5 in Height: 14-1/2 in Depth: 4-5/8 in H/CTR: 7-3/4 in

Clear glass Cylindrical Shade

Width: 2-3/8 in Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CULus Damp Location Listed
Wall Mounted	Trowned	One 60 W max. Candelabra Base	colas bamp location listed
Mounting plate for outlet box	6 inches of wire supplied	or LED equivalent	1-year Limited Warranty
included			
	120 V	E12 base Phenolic socket	
Canopy covers a standard 4"			
recessed outlet box: 5" W., 9" ht.,			
1.125" depth			
1.125 depth			