

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P710085-163 Hinton

Enjoy focused task lighting with the industrial demeanor of this one-light swing arm wall bracket. A metal shade is ready to provide you with focused task light wherever illumination is called upon. The light fixture's signature adjustable arm is coated in a vintage brass finish and makes this wall light a favorite choice for when you want to read your favorite novel before bed.

- A metal shade is ready to provide you with focused task light wherever illumination is called upon.
- The light fixture's signature adjustable arm is coated in a vintage brass finish and makes this wall light a favorite choice for when you want to read your favorite novel before bed.
- A smooth simple knob serves as the light fixture's rotating on/off switch.
- Ideal for any bedroom, living room, or sitting room.
- Perfect for transitional, farmhouse, coastal, and vintage electric settings.
- Measures 8-1/4-inch width by 9-5/8-inch height.
- Uses one medium base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Wall Brackets

Finish: Vintage Brass (Plated)

Construction: Steel Construction

Glass/Shade: Vintage Brass steel Cone shaped shade



Width: 8-1/4 in
Height: 9-5/8 in
Depth: 12-1/8 in
H/CTR: 3-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: one 60 W max. A-19 or LED equivalent	cCSAus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	E26 base Porcelain socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.5" ht., 0.75" depth	120 V		