

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P710089-009 Chadwick

Stick with simple geometric forms and clean crisp lines with this modern wall bracket. A beautiful opal glass shade visually calms the sharp edges of the boxy frame in a masterful stroke of design excellence. The frame is coated in a classic brushed nickel finish that contrasts the light shade. The light fixture is just right for spaces in need of a subtle, feminine touch.

- A beautiful opal glass shade visually calms the sharp edges of the boxy frame in a masterful stroke of design excellence.
- The frame is coated in a classic brushed nickel finish that contrasts the light shade.
- The light fixture is just right for spaces in need of a subtle, feminine touch.
- Ideal for any foyer, dining room, hallway, bathroom, or kitchen.
- Perfect for transitional, modern, and contemporary settings.
- Measures 5-1/2-inch width by 18-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Wall Brackets

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Opal glass Cylindrical Shade



Width: 5-1/2 in  
Height: 18 in  
Depth: 5.38 in  
H/CTR: 14-1/4 in (glass facing up)

Etched Opal glass Cylindrical Shade  
Width: 4-5/16 in  
Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CULus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	One 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 5.5" W., 6.375" ht., 0.75" depth			